



Weldon element with compensation, long, For nominal \varnothing d: 9mm



Order data

Order number	335725 9
GTIN	4045197801586
Item class	32P

Description

Version:

Plain toolholder, hardened and ground with **quick-release coupling**. Internal square to take taps and transmit the torque. Clamping mechanism prevents the tap being pulled out. Tensile/compression compensation each of 0.2 mm by means of compensation element. Clamping of the Weldon element either by means of the drive flats or the compensation element.

Advantage:

- **Attractively priced solution.**
- **Sturdy, slim version.**
- **Variation in the clamping and overhang lengths.**

Application:

To take taps and others in a Weldon arbor.

Optional extras:

Compensation element No. 335730.

Note:

Minimum compensation function **only** in combination with No. 300415 and 335730. The standard Weldon chuck permits only rigid clamping, see No. 335740.

Technical description

External \varnothing D	18 mm
Overhang A	141.5 mm
Adjustment travel V	10 mm
Clamping range d	9 mm
Overall length L	148 mm

Type of product

Tapping head