

**Weldon element with compensation, long, For nominal  $\varnothing$  d: 6mm****Order data**

Order number	335725 6
GTIN	4045197801616
Item class	32P

**Description****Version:**

Plain toolholder, hardened and ground with **quick-release coupling**. Internal square to take taps and transmit the torque. Clamping mechanism prevents the tap being pulled out. Tensile/compression compensation each of 0.2 mm by means of compensation element. Clamping of the Weldon element either by means of the drive flats or the compensation element.

**Advantage:**

- **Attractively priced solution.**
- **Sturdy, slim version.**
- **Variation in the clamping and overhang lengths.**

**Application:**

To take taps and others in a Weldon arbor.

**Optional extras:**

Compensation element No. 335730.

**Note:**

Minimum compensation function **only** in combination with No. 300415 and 335730. The standard Weldon chuck permits only rigid clamping, see No. 335740.

**Technical description**

External $\varnothing$ D	14 mm
Overhang A	137 mm
Clamping range d	6 mm
Adjustment travel V	10 mm
Overall length L	145 mm

Type of product

Tapping head