



MultiMaster FMM 350 Q, Type: 72295261



Order data

Order number	077814 72295261
GTIN	4014586884578
Item class	03F

Description

Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

MultiMaster – powerful, universal orbital machines.

- **Extremely smooth cutting action.**
- **Anti-vibration system with robust motor (housing decoupling).**

Power supply adapters with convenient cable length (5 m). **Top** – with complete equipment including comprehensive abrasive accessories.

Standard:

MultiMaster – powerful, universal orbital machines.

- **Very smooth cutting action.**
- **Anti-vibration system with robust motor (housing decoupling).**
- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **QuickIN quick-release clamping system (quicker tool change times, no wrench required)**

- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Supplied with:

1 tool case set **"Top"** with 2 abrasive plates (1 × perforated and 1 × unperforated), 3 each abrasive sheets perforated and unperforated (K 60, 80, 120, 180), 1 backing disc Ø 115 mm perforated, 2 each abrasive sheets perforated (K 60, 80, 180), 1 dust extractor, 1 fixed spatula, 1 E-Cut Long-Life saw blade (35 mm), 1 universal E-Cut saw blade (44 mm), 1 E-Cut Long-Life saw blade (65 mm), 1 HSS segmented saw blade, 1 carbide saw blade, 1 carbide rasp (3-square shape) perforated.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Packaging: Carrying case

Manufacturer's designation: FMM 350 QSL Top

Power consumption: 350 W

Toolholder: StarlockPlus, Starlock

Speed of oscillation: 10000 - 19500 rpm

Amplitude (oscillation movement): 2 × 1.7 degrees

Width across grinding plate head: 80 mm

Technical description

Speed of oscillation	10000 - 19500 rpm
Power consumption	350 W
Cable length	5 m
Width across grinding plate head	80 mm
Weight	1.4 kg
Manufacturer's designation	FMM 350 QSL Top
Toolholder	StarlockPlus, Starlock
Amplitude (oscillation movement)	2 × 1.7 degrees
Packaging	Carrying case