



MultiTalent FMT 250Q, Type: 72295361



Order data

Order number	077824 72295361
GTIN	4014586884905
Item class	03F

Description

Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

MultiTalent FMT 250Q mains adapter in a case. **Cordless variant with battery** No. 077825 size 71291561 **available on request from October 2015.**

Supplied with:

1 toolbox set "**QuickStart**" containing: 1 abrasive plate, 3 each abrasive discs (80, 120, 180 grit), 1 E-Cut universal saw blade (44 mm).

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Packaging: Carrying case

Manufacturer's designation: FMT 250 QSL QuickStart

Power consumption: 250 W

Toolholder: StarlockPlus, Starlock

Speed of oscillation: 11000 - 20000 rpm

Amplitude (oscillation movement): 2 × 1.6 degrees
Width across grinding plate head: 80 mm

Technical description

Cable length	5 m
Width across grinding plate head	80 mm
Weight	1.4 kg
Manufacturer's designation	FMT 250 QSL QuickStart
Speed of oscillation	11000 - 20000 rpm
Power consumption	250 W
Toolholder	StarlockPlus, Starlock
Amplitude (oscillation movement)	2 × 1.6 degrees
Packaging	Carrying case