

**MultiMaster AFMM Cordless, Type: 71292261****Order data**

| | |
|--------------|-----------------|
| Order number | 077815 71292261 |
| GTIN | 4014586884066 |
| Item class | 03F |

Description**Version:**

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

MultiMaster – powerful, universal orbital machines.

- **Extremely smooth cutting action.**
- **Anti-vibration system with robust motor (housing decoupling).**

Cordless device of the latest generation with the same performance as mains-powered devices.

Supplied with:

1 toolbox set "**Akku (Battery)**" with: 2×Li-ion batteries, charger. 1 abrasive plate. 3 each saw blades (K 60, 80, 120, 180), 1 fixed scraper, 1 HSS segmented saw blade, 1 E-Cut long-life saw blade (65 mm), 1 E-Cut universal saw blade (44 mm).

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073835 ff and 073845 for suitable spare batteries and chargers.

Packaging: Carrying case
 suitable battery - supplier / battery type / voltage: Fein type E 18 V
 Manufacturer's designation: AFMM 18 QSL
 Battery voltage: 18 V
 Battery capacity: 3 A·h
 Toolholder: StarlockPlus, Starlock
 Speed of oscillation: 11000 - 18500 rpm
 Amplitude (oscillation movement): 2 × 1.7 degrees

Technical description

| | |
|--|------------------------|
| Width across grinding plate head | 80 mm |
| Manufacturer's designation | AFMM 18 QSL |
| Battery capacity | 3 A·h |
| Weight | 1.8 kg |
| Battery voltage | 18 V |
| Speed of oscillation | 11000 - 18500 rpm |
| Amplitude (oscillation movement) | 2 × 1.7 degrees |
| Toolholder | StarlockPlus, Starlock |
| Number of rechargeable batteries contained | 2 |
| Type of rechargeable battery | Lithium-ion |
| Packaging | Carrying case |
| suitable battery - supplier / battery type / voltage | Fein type E 18 V |

Accessories

| | |
|---|-------------|
| Battery charger Type FE30 | 073845 FE30 |
| Battery charger Type FE50 | 073845 FE50 |
| Li-ion battery Battery type, battery voltage FE18 V | 073836 FE18 |