



Current and voltage tester, Type: 755-1



Order data

Order number	473220 755-1
GTIN	4029547013928
Item class	47B

Description

Version:

Ergonomic plastic housing with non-slip ring, rubberised gripping area and measuring prod clips. **Fully automatic measurement of current, voltage and resistance.** Exchangeable test prods. Integral torch for illuminating the measurement area.

Function:

IP64: Protected against splashed water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

For professional voltage and polarity testing, and for current measurement. Suitable for working on electrical systems, industrial systems, maintenance and servicing (troubleshooting).

Standard:

DIN EN 61243-3:2014, EN 61010-1:2011.

Supplied with:

Incl. batteries No. 081561 size LR3, measurement prods and measurement prod extensions.

Technical description

Continuity testing	yes
--------------------	-----

Resistance	1 Ω - 100 kΩ
Information displayed	4000
Illumination of probe points	yes
AC current	0.1 - 200 A
IP Index of Protection	IP 64
Calibration	I4
DC voltage	6 V – 600 V
Overvoltage category	CAT III 1000 V; CAT IV 600 V
AC voltage	6 V – 600 V
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Type of product	Multimeter

Services

DAkkS calibrationClamp meter Type D	027060 D
CalibrationClamp meter Type D	027050 D

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------