



Multimeter, Type: 760-1



Order data

Order number	473310 760-1
GTIN	4029547013942
Item class	47B

Description

Version:

Sturdy plastic casing with large illuminated LCD display and rubberised gripping area.

Automatic detection of the units of measurement, based on the socket assignment.

Automatic setting of the measurement range and type of measurement (AC/DC). Simple error-avoiding operation with illuminated function keys.

Function:

IP64: Protected against splashed water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

Suitable for a wide range of field of application in electrical technology, industrial systems, maintenance, servicing (troubleshooting),

Standard:

DIN EN 61326-1, EN 61010-2-033

Supplied with:

3 batteries No. 081561 size LR3 and measurement leads.

Technical description

DC voltage	0.1 mV – 600 V
DC current	1 mA - 10 A
Diode testing	yes
Overvoltage category	CAT IV 300 V; CAT III 600 V
Resistance	0.1 - 40 MΩ
Frequency	0.001 Hz - 512 kHz
Capacitance	0.001 nF - 100 μF
IP Index of Protection	IP 64
Continuity testing	yes
Basic accuracy	0.8 %
AC voltage	0.1 mV – 600 V
AC current	1 mA - 10 A
Calibration	I3
Information displayed	4000
Number of batteries contained	3
Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Standard	DIN EN 61326-1
Standard	EN 61010-2-033
Type of product	Multimeter

Services

CalibrationDigital multimeter Number of decimal places 3	027000 3
DAkkS calibrationDigital multimeter Number of decimal places 3	027010 3

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------