



Multimeter, Type: 760-3



Order data

Order number	473310 760-3
GTIN	4029547013966
Item class	47B

Description

Version:

Sturdy plastic casing with large illuminated LCD display and rubberised gripping area.

Automatic detection of the units of measurement, based on the socket assignment.

Automatic setting of the measurement range and type of measurement (AC/DC). Simple error-avoiding operation with illuminated function keys.

Function:

IP64: Protected against splashed water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

Suitable for a wide range of field of application in electrical technology, industrial systems, maintenance, servicing (troubleshooting),

Standard:

DIN EN 61326-1, EN 61010-2-033

Supplied with:

3 batteries No. 081561 size LR3 and measurement leads.

Technical description

Basic accuracy	0.1 %
Capacitance	0.001 nF - 60000 μ F
DC current	0.1 μ A - 10 A
IP Index of Protection	IP 64
Resistance	0.1 - 60 M Ω
Frequency	0.001 Hz – 60 MHz
Continuity testing	yes
Calibration	I3
Information displayed	6000
AC current	0.1 μ A - 10 A
Temperature	-20 - 500 $^{\circ}$ C
Diode testing	yes
Overvoltage category	CAT IV 600 V; CAT III 1000 V
Measurement process	TRUE RMS
DC voltage	0.1 mV – 1000 V
AC voltage	0.1 mV – 1000 V
Number of batteries contained	3
Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Standard	DIN EN 61326-1
Standard	EN 61010-2-033
Type of product	Multimeter

Services

CalibrationDigital multimeter Number of decimal places 3	027000 3
DAkkS calibrationDigital multimeter Number of decimal places 3	027010 3

Accessories

Alkaline-manganese batteries International size LR3

081561 LR3