



Digital current clamp, Type: 770-1



Order data

Order number	473315 770-1
GTIN	4029547013973
Item class	47B

Description

Version:

Sturdy plastic casing with large illuminated LCD display and rubberised gripping area.

Unique gripping mechanism facilitates work in restricted spaces. **Automatic setting of the measurement range and type of measurement (AC/DC)**. With μA measurement range for measuring ionisation currents (with measurement leads).

Application:

Suitable for a wide range of field of application in electrical technology, industrial systems, maintenance, servicing (troubleshooting),

Standard:

EN 61326-1, EN 61140.

Supplied with:

3 batteries No. 081561 LR3 and test leads.

Technical description

DC current	0.1 A - 400 A
AC voltage	1 mV – 600 V

Basic accuracy	0.8 %
Frequency	0.001 Hz - 10 kHz
Resistance	0.1 - 40 MΩ
Measurement process	TRUE RMS
Information displayed	4000
DC voltage	1 mV – 600 V
Overvoltage category	CAT III 1000 V; CAT IV 600 V
AC current	0.1 A - 400 A
Continuity testing	yes
Diode testing	yes
Capacitance	0.001 μF - 100 μF
Number of batteries contained	3
Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Power supply	3× No. 081561 size LR3
Calibration	I4
Type of product	Current clamp

Services

DAkkS calibrationClamp meter Type D	027060 D
CalibrationClamp meter Type D	027050 D

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------