

**Electronics flat-nose pliers, overall length: 115mm****Order data**

Order number	727190 115
GTIN	4003773035107
Item class	73F

Description**Version:**

Mirror polished, therefore no faults in the circuit due to peeling chrome plate. Precision box joint. Low-friction double spring for smooth and gentle opening. Gripping faces ground smooth. Edges carefully deburred.

Handles with multi-component coating.

Application:

For precision assembly work, e.g. in electronics and precision mechanisms.

Standard:

DIN ISO 9655

Material:

Ball-bearing steel, oil quenched.

Note:

Further versions available on request.

Technical description

Type of jaws	inside ground smooth
Head width	9.5 mm
overall length	115 mm
Jaw length	22.5 mm
Jaw design	flat, straight
Standard	DIN ISO 9655

Handle	Multi-component covering
Material	Ball-bearing steel
Surface	mirror polished
with return spring	yes
Type of product	Flat-nose pliers