



## Electronics snipe-nosed pliers, overall length: 115mm



### Order data

Order number	727196 115
GTIN	4003773024842
Item class	73F

### Description

**Version:**

Mirror polished, therefore no faults in the circuit due to peeling chrome plate. Precision box joint. Low-friction double spring for smooth and gentle opening. Multi-component grips, black/grey, electrically conductive. **Suitable for ESDs.** Gripping faces ground smooth. Edges carefully deburred.

**Application:**

For precision assembly work, e.g. in electronics and precision mechanisms.

**Standard:**

DIN ISO 9655

**Material:**

Ball-bearing steel, oil quenched.

**Note:**

Further versions available on request.

### Technical description

Jaw length	22.5 mm
overall length	115 mm
Head width	9.5 mm
electrostatic characteristic	EGB/ESD
Jaw design	taper to a point.
Standard	DIN ISO 9655

Type of jaws	inside ground smooth
Handle	Multi-component covering
Material	Ball-bearing steel
Surface	mirror polished
with return spring	yes
Type of product	Snipe nose pliers