



Electronics side cutter, mirror-polished, round head, FW, overall length: 115mm



Order data

Order number	726430 115
GTIN	4003773039334
Item class	73F

Description

Version:

Mirror polished, therefore no faults in the circuit due to peeling chrome plate. Sturdy box joint with zero play. Low-friction double spring for smooth and gentle opening. Handles with multi-component coating.

Application:

For making precision cuts, e.g. in electronics and precision mechanisms.

Standard:

DIN ISO 9654

Material:

Ball-bearing steel, cutting edges induction hardened.

Technical description

Cutting capacity copper wire up to Ø	0.3 - 1.6 mm
overall length	115 mm
Head width	11 mm
Cutting capacity hard wire up to Ø	0.3 - 0.6 mm
Cutter length	14 mm
Cutting capacity medium hard wire up to Ø	0.3 - 1.2 mm
Cutting chamfer	fine bevel

Material	Ball bearing steel
Head shape	round
Standard	DIN ISO 9654
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Surface	mirror polished
Product name attribute	FW
with return spring	yes
Type of product	Cutting pliers