

**Electronics side cutter, mirror-polished, pointed head, FW, overall length: 115mm****Order data**

Order number	726436 115
GTIN	4003773025122
Item class	73F

**Description****Version:**

Mirror polished, therefore no faults in the circuit due to peeling chrome plate. Sturdy box joint with zero play. Low-friction double spring for smooth and gentle opening. Multi-component grips, black/grey, electrically conductive. **Suitable for ESDs.**

**Application:**

For making precision cuts, e.g. in electronics and precision mechanisms.

**Standard:**

DIN ISO 9654

**Material:**

Ball-bearing steel, cutting edges induction hardened.

**Technical description**

Head width	11 mm
Cutting capacity copper wire up to Ø	0.3 - 1.3 mm
Cutting capacity hard wire up to Ø	0.3 - 0.5 mm
overall length	115 mm
Cutter length	14 mm
Cutting capacity medium hard wire up to Ø	0.3 - 1 mm
electrostatic characteristic	EGB/ESD

Cutting chamfer	fine bevel
Material	Ball bearing steel
Head shape	pointed
Standard	DIN ISO 9654
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 62 HRC)
Surface	mirror polished
Product name attribute	FW
Type of product	Cutting pliers