

**Garant**
**Centring vice, neutral, Jaw width A: 80mm**

**Order data**

Order number	360133 80
GTIN	4045197801296
Item class	310

**Description**
**Version:**

Centring vice for flexible applications.

- **Absolute operational reliability thanks to enclosure.**
- **High repetition accuracy 0.02 mm.**
- **Variable central alignment  $\pm 0.02$  mm.**
- **Functional faces hardened.**
- **Sturdy design of tool steel, surface protection by brief exposure nitriding.**

**Advantage:**

Multi-functional uses.

- **Flexible lightweight.**

**Application:**

Ideal for 5-face machining, perfect for clamping blank parts.

**Suitable for:**

Directly on the machine table, exchange pallet or 3-way extension base No. 360156.

**Supplied with:**

Supplied with socket No. 642700 size E12.

2 table clamps.

**Optional extras:**

Types of jaws No. 360135– 360151.

**Technical description**

Clamping force up to maximum	17 kN
Width	80 mm
Stroke	22 mm
Jaw width A	80 mm
Height	50.2 mm
Length	110 mm
Torque	40 Nm
Weight	2.5 kg
suitable for colour code	ZC 80
Type of product	Machine vice

## Accessories

Pair of gripp top jaws for type 80	360143 80
Pair of carbide top jaws for type 80	360135 80
Pair of carbide top jaws for type 80	360138 80
Pair of Vee jaws for type 80	360148 80
Pair of carbide top jaws for type 80	360136 80
Pair of soft top jaws for type 80	360145 80
Pair of gripp top jaws for type 80	360142 80
Pair of gripp top jaws for type 80	360140 80
Pair of soft top jaws for type 80	360146 80
Pair of carbide top jaws for type 80	360137 80
Pair of gripp top jaws for type 80	360141 80