

Garant**Centring vice, neutral, Jaw width A: 120mm****Order data**

Order number	360133 120
GTIN	4045197801906
Item class	310

Description**Version:**

Centring vice for flexible applications.

- **Absolute operational reliability thanks to enclosure.**
- **High repetition accuracy 0.02 mm.**
- **Variable central alignment ± 0.02 mm.**
- **Functional faces hardened.**
- **Sturdy design of tool steel, surface protection by brief exposure nitriding.**

Advantage:

Multi-functional uses.

- **Flexible lightweight.**

Application:

Ideal for 5-face machining, perfect for clamping blank parts.

Suitable for:

Directly on the machine table, exchange pallet or 3-way extension base No. 360156.

Supplied with:

Supplied with socket No. 642700 size E12.

2 table clamps.

Optional extras:

Types of jaws No. 360135– 360151.

Technical description

Stroke	25 mm
Width	120 mm
Torque	60 Nm
Clamping force up to maximum	25.5 kN
Height	50.2 mm
Length	130 mm
Weight	5.1 kg
Jaw width A	120 mm
suitable for colour code	ZC120
Type of product	Machine vice

Accessories

Pair of gripp top jaws for type 120	360143 120
Pair of carbide top jaws for type 120	360136 120
Pair of carbide top jaws for type 120	360138 120
Pair of carbide top jaws for type 120	360135 120
Pair of Vee jaws for type 120	360148 120
Pair of gripp top jaws for type 120	360141 120
Pair of soft top jaws for type 120	360145 120
Pair of gripp top jaws for type 120	360140 120