



Digital workshop caliper IP67 without measuring tips, Measuring range: 300mm



Order data

Order number	415366 300
GTIN	2050001894014
Item class	46P

Description

Version:

Very large high-contrast LCD display. Digit height 8 mm or 14 mm (from size 500 mm). With preset (dimension selection in advance). The caliper is resistant to water, emulsion, oil, and dust.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Incl. battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948 size USB2.

Technical description

Scale divisions	0.0005 in
Internal jaw \varnothing	10 mm
Error limit	0.03 mm
Calibration	A1
Scale divisions	0.01 mm
Reversible reading	mm / inch
Jaw length	100 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032

Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Standard	Works standard
Interface	USB interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Connection cable Type USB2	498948 USB2