



## “CYL-3” carbide masonry drill, Drill Ø: 3,5 mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 786005 3,5    |
| GTIN         | 3165140462266 |
| Item class   | 76K           |

### Description

#### Version:

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

**Hammer and rotary bits** with strong carbide cutter tip.

#### Application:

Primarily for **drilling dowel holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic. Also suitable for drilling hardened steel due to corrected cutting edge.

Shank: Plain shank

Flute length: 40 mm

overall length: 70 mm

Shank Ø: 3.5 mm

### Technical description

|                           |          |
|---------------------------|----------|
| Drill Ø                   | 3.5 mm   |
| Number of cutting edges Z | 2        |
| Shank Ø                   | 3.5 mm   |
| overall length            | 70 mm    |
| Flute length              | 40 mm    |
| Tool material             | Carbide  |
| Standard                  | ISO 5468 |
| Standard                  | DIN 8039 |

|                                  |                 |
|----------------------------------|-----------------|
| Use with impact / without impact | Impact drilling |
| Shank                            | Plain shank     |
| Type of product                  | Masonry drill   |