

## "CYL-3" carbide masonry drill, Drill Ø: 5,5 mm



### **Order data**

Order number	786005 5,5
GTIN	3165140186711
Item class	76K

## **Description**

#### **Version:**

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

**Hammer and rotary bits** with strong carbide cutter tip.

### **Application:**

Primarily for **drilling dowel holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic. Also suitable for drilling hardened steel due to corrected cutting edge.

Shank: Plain shank Flute length: 50 mm overall length: 85 mm Shank Ø: 5.5 mm

# **Technical description**

overall length	85 mm
Shank Ø	5.5 mm
Number of cutting edges Z	2
Flute length	50 mm
Drill Ø	5.5 mm
Tool material	Carbide
Standard	ISO 5468
Standard	DIN 8039

Use with impact / without impact	Impact drilling
Shank	Plain shank
Type of product	Masonry drill