

**"CYL-3" carbide masonry drill, Drill Ø: 16 mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 786005 16     |
| GTIN         | 3165140186834 |
| Item class   | 76K           |

**Description****Version:**

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

**Hammer and rotary bits** with strong carbide cutter tip. With reduced shank.

**Application:**

Primarily for **drilling dowel holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic. Also suitable for drilling hardened steel due to corrected cutting edge.

Shank: Plain shank

Flute length: 100 mm

overall length: 160 mm

Shank Ø: 12.3 mm

**Technical description**

|                           |          |
|---------------------------|----------|
| overall length            | 160 mm   |
| Drill Ø                   | 16 mm    |
| Flute length              | 100 mm   |
| Number of cutting edges Z | 2        |
| Shank Ø                   | 12.3 mm  |
| Tool material             | Carbide  |
| Standard                  | ISO 5468 |
| Standard                  | DIN 8039 |

|                                  |                 |
|----------------------------------|-----------------|
| Use with impact / without impact | Impact drilling |
| Shank                            | Plain shank     |
| Type of product                  | Masonry drill   |