



“CYL-9” carbide-tipped multi-purpose drill, Drill Ø: 12 mm



Order data

| | |
|--------------|---------------|
| Order number | 787005 12 |
| GTIN | 3165140044882 |
| Item class | 76K |

Description

Version:

Carbide tip **with ground point and multi-purpose cutter angle**. The **centrally ground chisel edge** ensures accurate spot drilling also on hard surfaces. Shank of annealed special steel.

Application:

For drilling various materials, in a single operation:

- **Bricks, porous concrete, lightweight materials, plastics.**
- **Tiles, ceramics, marble, glass**
- **Reinforcing bars in concrete.**

Note:

- **Caution: only for rotary use (without hammer action!)**
- **Faster drilling and more holes per battery charge than with hammer drill bits.**

Shank: Plain shank

Flute length: 90 mm

overall length: 150 mm

Technical description

| | |
|----------------------------------|-------------------------|
| Flute length | 90 mm |
| Number of cutting edges Z | 2 |
| overall length | 150 mm |
| Drill Ø | 12 mm |
| Tool material | Carbide |
| Use with impact / without impact | not for impact drilling |
| Shank | Plain shank |
| Type of product | Multi-purpose drill |

