

 Mahr**Digital groove depth gauge IP67, Measuring range: 200mm****Order data**

Order number	418753 200
GTIN	4059192057343
Item class	43A

Description**Version:**

For measuring cut-outs, grooves, recesses, shoulders etc. Measuring beam with double hook. Both contact faces in a single plane.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498940.

Technical description

Calibration	A2
Measuring range	0 - 200 mm
Bridge length	100 mm
Reversible reading	mm / inch
Reversible reading	0.0005 in
Reversible reading	0.01 mm
Cross-section measuring beam	11.5 × 3.6 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032

Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	± 0.03 mm
Standard	ISO 13385
Interface	Digimatic interface
Interface	RS232 interface
Interface	USB interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Material	Stainless steel, INOX
Packaging	sturdy box
Type of product	Groove depth gauge

Services

DAkkS calibration Vernier hook depth gauge maximum measuring range 200 mm	021230 200
Calibration Vernier hook depth gauge maximum measuring range 200 mm	021220 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Battery compartment cover	412235