

 Mahr**Digital groove depth gauge IP67, Measuring range: 300mm****Order data**

Order number	418753 300
GTIN	4059192057350
Item class	43A

Description**Version:**

For measuring cut-outs, grooves, recesses, shoulders etc. Measuring beam with double hook. Both contact faces in a single plane.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498940.

Technical description

Reversible reading	mm / inch
Measuring range	0 - 300 mm
Reversible reading	0.0005 in
Bridge length	150 mm
Cross-section measuring beam	11.5 × 3.6 mm
Calibration	A2
Reversible reading	0.01 mm
Number of batteries contained	1

Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	± 0.04 mm
Standard	ISO 13385
Interface	Digimatic interface
Interface	RS232 interface
Interface	USB interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Material	Stainless steel, INOX
Packaging	sturdy box
Type of product	Groove depth gauge

Services

Calibration Vernier hook depth gauge maximum measuring range 300 mm	021220 300
DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	021010 300

Accessories

Battery compartment cover	412235
Button cell / special battery Battery type CR2032	081560 CR2032