



## Two-speed power drill, Type: 720554



### Order data

Order number	075150 720554
GTIN	4014586882512
Item class	03F

### Description

#### Version:

- **Compact 2-speed power drill for drilling, countersinking, tapping, and screwdriving.**
- **Stepless electronic speed control for gentle starts to drilling and screwdriving.**
- **Integral switch with clockwise / anticlockwise switch for ease of use.**

Additional serrated handle for secure holding (positive grip).

#### Supplied with:

Quick-clamping drill chuck with locking force safety device, 1 additional handle.

#### Attention:

German version. Order free UK adapter plug No. 08 1172\_GB.

#### Note:

For suitable twist drills see No. 114000 ff.

Manufacturer's designation: BOP 10-2

Power consumption: 500 W

Speed range 1st speed: 0 - 700 rpm

Speed range 2nd speed: 0 - 2250 rpm

Drill chuck adapter: 1/2 inch – 20 UNF

Chuck clamping range: 1.5 - 13 mm

### Technical description

maximum twist drill size Ø in wood 2nd speed	25 mm
Power consumption	500 W

maximum twist drill size Ø in wood 1st speed	35 mm
Manufacturer's designation	BOP 10-2
Maximum twist drill size Ø in steel 1st speed	10 mm
Drill chuck adapter	1/2 inch – 20 UNF
maximum twist drill size Ø in steel 2nd speed	8 mm
Weight	2 kg
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Chuck clamping range	1.5 - 13 mm
Speed range 1st speed	0 - 700 rpm
Speed range 2nd speed	0 - 2250 rpm