

**HOLEX****Digital groove depth gauge, Measuring range: 100mm****Order data**

Order number	418755 100
GTIN	4045197801890
Item class	42A

**Description****Version:**

Digital depth gauge for measuring slots, grooves, recesses, offsets and holes. Weight-saving construction of aluminium profile reinforced with steel, with anodised surfaces. Optimum guidance and sliding characteristics due to internal double Vee guides. Various different measuring tips (M2.5) can be screwed into the measuring rod.

Aluminium profile with steel reinforcement and anodised surface. Double Vee guides.

Exchangeable measuring tips (M2.5).

**Application:**

Measuring cut-outs, grooves, holes and offsets.

**Supplied with:**

Measuring tip with steel ball, disc insert No. 434900 size 11, measurement heads 150 mm and 350 mm, battery No. 081560 size LR44.

**Note:**

Measurement heads 550 mm, 750 mm and 900 mm on request.

**Technical description**

Disc anvil $\varnothing$	10 mm
Measuring range	0 - 100 mm
Reversible reading	mm / inch
Measuring rod $\varnothing$	4 mm
Error limit	0.03 mm
Cross-section measuring beam	23.5 × 9 mm

Calibration	A1
Article no of the battery / rechargeable battery fitted	081560 LR44
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Measurement technology	digital
Test certificate	Manufacturer's test certificate
Packaging	sturdy box
Type of product	Groove depth gauge

## Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

## Accessories

Button cell / special battery Battery type LR44	081560 LR44
---	-------------