



Stepped jaw for gripp inserts movable, for type: 125



Order data

Order number	361347 125
GTIN	4250364402729
Item class	34A

Description

Application:

For clamping blanks and finished parts (using screw-in gripp inserts).

Suitable for:

Titan 2 No. 361302.

Note:

Blanks can be clamped only if they are parallel workpieces. Gripp inserts No. 361238 – 361250.

Technical description

Length l_1	40 mm
suitable for colour code	Titan2/TitanSense
suitable for colour code	Titan
suitable for colour code	LCV125G
Jaw width b	124.4 mm
Jaw height h	39.5 mm
Jaw length l	70 mm
Height h_1	20 mm
Type of product	Vice jaws

