



Stepped jaw for gripp inserts movable, for type: 160



Order data

Order number	361347 160
GTIN	4250364402989
Item class	34A

Description

Application:

For clamping blanks and finished parts (using screw-in gripp inserts).

Suitable for:

Titan 2 No. 361302.

Note:

Blanks can be clamped only if they are parallel workpieces. Gripp inserts No. 361238 – 361250.

Technical description

Length l_1	64 mm
Height h_1	25 mm
Jaw width b	160.4 mm
suitable for colour code	TitanSense
Jaw height h	49.8 mm
Jaw length l	114 mm
Type of product	Vice jaws

