



## Stepped jaw for gripp inserts fixed, for type: 160



### Order data

Order number	361348 160
GTIN	4250364402996
Item class	34A

### Description

#### Application:

For clamping blanks and finished parts (using screw-in gripp inserts).

#### Suitable for:

Titan 2 No. 361302.

#### Note:

Blanks can be clamped only if they are parallel workpieces. Gripp inserts No. 361238 – 361250.

### Technical description

Jaw height h	49.8 mm
Height $h_1$	25 mm
Length $l_1$	44 mm
suitable for colour code	TitanSense
Jaw length l	104 mm
Jaw width b	160.4 mm
Type of product	Vice jaws

