


Garant**Flap wheel (CER), 60 grit, Head Ø×head width: 60X30mm****Order data**

Order number	554150 60X30
GTIN	4045197803818
Item class	51E

Description**Version:**

Flap strips bonded on to the shank of the tool.
Abrasive strips covered with **ceramic grit (CER)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Technical description

Head Ø	60 mm
Shank Ø	6 mm
recommended speed	8000 min ⁻¹
Head width	30 mm
maximum speed	12700 min ⁻¹
Grit	60
Grinding media	Ceramic grit (CER)

Grinding medium code	Ceramic
Product name attribute	60 grit
Type of product	Flap wheel

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable only under restricted conditions		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		