

BMI®**Tape measure Vario, accuracy class 1, Tape length: 5m****Order data**

| | |
|--------------|---------------|
| Order number | 462090 5 |
| GTIN | 4007368112242 |
| Item class | 46M |

Description**Version:**

A particularly lightweight and handy tape measure for professional use. Body of glass fibre-reinforced polyamide. **With push button for tape lock and automatic return.** Plain bearing of special TRIBOCOMP® material with Teflon ensures **smooth gliding** and exceptionally easy running. Innovative dampers of special rubber absorb the reaction energy and protect the wrist. A special clear lacquer protects the tape against wear. The **additional anti-glare correction** ensures clear visibility under all light conditions.

Technical description

| | |
|-----------------|----------------|
| Body width | 26 mm |
| Band length | 5 m |
| Body length | 75 mm |
| Tape width | 16 mm |
| Body height | 70 mm |
| Standard | EG I |
| Calibration | G1 |
| Type of product | Measuring tape |

Services

CalibrationTape measure maximum length 5 m

026240 5