

**Tape measure Vario, accuracy class 1, Tape length: 8m****Order data**

Order number	462090 8
GTIN	4007368112259
Item class	46M

**Description****Version:**

A particularly lightweight and handy tape measure for professional use. Body of glass fibre-reinforced polyamide. **With push button for tape lock and automatic return.** Plain bearing of special TRIBOCOMP® material with Teflon ensures **smooth gliding** and exceptionally easy running. Innovative dampers of special rubber absorb the reaction energy and protect the wrist. A special clear lacquer protects the tape against wear. The **additional anti-glare correction** ensures clear visibility under all light conditions.

**Technical description**

Band length	8 m
Tape width	19 mm
Body height	75 mm
Body length	76 mm
Body width	32 mm
Standard	EG I
Calibration	G1
Type of product	Measuring tape

---

## Services

CalibrationTape measure maximum length 10 m

026240 10