

AEG

Cordless drill / driver, Type: BS14G3



Order data

Order number	070221 BS14G3
GTIN	4002395811199
Item class	07A

Description

Version:

AEG – Cordless drill / driver

- Sturdy and handy cordless 2-speed drill / screwdriver, reversible.
- FIXTEC quick-change chuck with spindle lock.
- Handle with Softgrip coating for comfortable use.
- LED illumination of the working area.
- 23-step torque limit adjustment, plus drill steps.
- 13 mm quick-change chuck.

Standard:

- Sturdy and handy cordless 2-speed drill / driver, reversible.
- FIXTEC quick-change chuck with spindle lock.
- Handle with Softgrip coating for comfortable use.

Supplied with:

Supplied with charger, carrying case.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB. German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073820ff and No. 073841 for suitable spare batteries and chargers.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: AEG type C 14 V

Manufacturer's designation: BS 14 G3

Motor design: 2-pole motor

Battery capacity: 2 A·h

Battery voltage: 14.4 V

maximum torque hard: 36 N·m

maximum speed 1st speed: 0 - 400 rpm

Technical description

maximum vibration to EN	< 2.5 m/s ²
Manufacturer's designation	BS 14 G3
Battery voltage	14.4 V
maximum twist drill size Ø in steel	12 mm
maximum torque hard	36 N·m
Weight	1.5 kg
maximum speed 1st speed	0 - 400 rpm
Quick-clamping chuck range	1.5 - 13 mm
maximum twist drill size Ø in wood	32 mm
suitable battery - supplier / battery type / voltage	AEG type C 14 V
Motor design	2-pole motor
Battery capacity	2 A·h
maximum speed 2nd speed	1700 rpm
typical application	Strong
Packaging	Carrying case

Accessories

Li-ion system GBS Rechargeable battery type, battery voltage AA14 V	073820 AA14
Battery charger Type BL1218	073841 BL1218
	073820 AC14

Li-ion system GBS Rechargeable battery type, battery
voltage AC14 V
