



Burr Z steel – coarse, Carbide, Type: D0807



Order data

Order number	540740 D0807
GTIN	4045197804839
Item class	52D

Description

Version:

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank \varnothing 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Technical description

Toothing grit designation	coarse
Shape description	ball
Overall length	52 mm
Head \varnothing	8 mm
Shape	D0807
Tooth type abbreviation	Z steel
Shank \varnothing	6 mm
Head length	7 mm
Series	Tooth configuration Z steel
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		