

**Burr Z steel – coarse, Carbide, Type: F0820****Order data**

Order number	540740 F0820
GTIN	4045197804877
Item class	52D

**Description****Version:**

**The innovative tooth geometry permits very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank  $\varnothing$  6 mm.

**Application:**

Optimised for **use on steel and steel castings**.

**Technical description**

Shape description	round arch
Tooting grit designation	coarse
Head $\varnothing$	8 mm
Shape	F0820
Shank $\varnothing$	6 mm
Overall length	65 mm

Tooth type abbreviation	Z steel
Head length	20 mm
Series	Tooth configuration Z steel
Tool material	Carbide
Type of product	Burr

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		