

**Burr Z steel – coarse, Carbide, Type: F1020****Order data**

Order number	540740 F1020
GTIN	4045197804884
Item class	52D

**Description****Version:**

**The innovative tooth geometry permits very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank  $\varnothing$  6 mm.

**Application:**

Optimised for **use on steel and steel castings**.

**Technical description**

Toothing grit designation	coarse
Head $\varnothing$	9.6 mm
Shape	F1020
Shape description	round arch
Tooth type abbreviation	Z steel
Overall length	64 mm

Shank Ø	6 mm
Head length	19 mm
Series	Tooth configuration Z steel
Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		