



Pneumatic straight grinder collet Ø 6 mm, Type: 3550-180



Order data

Order number	079453 3550-180
GTIN	015451785260
Item class	03R

Description

Version:

Pneumatic straight die grinder with 1050 W output power and a maximum speed of **18,000 rpm**.
Collet Ø 6 mm. Short version.

Technical description

Weight	1.2 kg
maximum vibration to EN	<2.5 m/s ²
maximum air consumption	1560 l/min
Output power	1050 W
Operating noise	81 dB(A)
Length	248 mm
Manufacturer's designation	3550-180
maximum speed	18000 min ⁻¹
Compressed air connection	1/4 in
Connection thread	NPT
Type of product	Straight die grinder

