



## Shoe, black/blue VD PRO 1500 SF, S3 NB BOA, EU shoe size: 39



### Order data

Order number	092587 39
GTIN	4044348608166
Item class	09C

### Description

#### Version:

**VARIO DYNAMICS® PRO** range of safety shoes. VARIO Multiflex® technology for less shoe weight.

- **Upper made of a very light microfibre.**
- **Breathable functional lining.**
- **TPU Athletic ESD outer sole, light blue.**
- **Real leather insole.**
- **ERGO-SOFT ESD comfort mid-sole inlay.**
- **Protection against electrostatic discharge (ESD).**

Shoe of seam-free construction. Dust tongue, appliques on the upper part of the shoe. With BOA® rotary catch.

#### Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

#### Note:

Wide version XB, see No. 092588.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Aluminium

Puncture resistance: Tekstil

Cold insulation: down to -20°C

Standard: Inlay type-tested according to DGUV regulation 191

Characteristics: Drejelukning

## Technical description

Standard	Inlay type-tested according to DGUV regulation 191
Cold insulation	down to -20°C
EU shoe size	39
Puncture resistance	Tekstil
Material of protective toe-cap	Aluminium
Protection class	S3
Characteristics	Drejelukning
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes