

**Drill, Type: GBM10RE****Order data**

Order number	075420 GBM10RE
GTIN	3165140485968
Item class	03B

Description**Version:**

Hand-held power drill with 600-W motor and high torque for holes up to 10 mm in steel.

- **Quick-release chuck for high precision and long working life.**
- **Compact design and low weight.**
- **Control electronics for exact starts to holes.**
- **Reversible.**
- **Softgrip.**

Advantage:

Control electronics for precise spot drilling.

Supplied with:

Including quick-clamping drill chuck, 10 mm.

Technical description

Manufacturer's designation	GBM 10 RE
maximum speed 1st speed	2600 min ⁻¹
Chuck clamping range	1 - 10 mm
Weight	1.7 kg
maximum twist drill size Ø in wood 1st speed	25 mm

maximum vibration to EN	4.8 m/s ²
Power consumption	600 W
Drill chuck adapter	1/2 inch – 20 UNF
Maximum twist drill size Ø in steel 1st speed	10 mm
Power supply	Mains operated
Suitable for material	Steel
Packaging	Modular case (L-Boxx)
Type of product	Drill