

**Hammer drill, Type: GBH220D****Order data**

Order number	075510 GBH220D
GTIN	3165140558914
Item class	03B

Description**Version:**

Sturdy hammer drill with **SDS-plus arbor** and high drill feed rate.

- **Overload clutch to protect both user and machine.**
- **Stepless speed control for responsive starts to drilling.**
- **Versatile application possibilities using the chisel function (zero rotation).**
- **Reversible, for releasing jammed drills.**
- **Impact action can be switched off for drilling in wood and steel.**

Supplied with:

With additional handle, machine cloth. Supplied with 210 mm depth stop, case.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

Suitable carbide hammer drills can be found under No. 787000 ff.

Packaging: Carrying case

Schaft: SDS Plus

Manufacturer's designation: GBH 2-20 D

Power consumption: 650 W

maximum twist drill size Ø in steel: 13 mm

maximum twist drill size Ø in wood: 30 mm

maximum twist drill size Ø in concrete: 20 mm

maximum hammer rate: 4200 rpm

Technical description

Manufacturer's designation	GBH 2-20 D
Power consumption	650 W
Tool arbor shape	SDS-Plus
maximum twist drill size Ø in concrete	20 mm
Impact energy	1.7 J
maximum twist drill size Ø in steel	13 mm
Weight	2.3 kg
maximum twist drill size Ø in wood	30 mm
maximum hammer rate	4200 rpm
maximum vibration to EN	13.5 m/s ²
Skaft	SDS Plus
Packaging	Carrying case

Accessories

Carbide-tipped multi-purpose drill Drill Ø 10 mm	787000 10
Carbide-tipped multi-purpose drill Drill Ø 12 mm	787000 12
Carbide-tipped multi-purpose drill Drill Ø 3 mm	787000 3
Carbide-tipped multi-purpose drill Drill Ø 4 mm	787000 4
Carbide-tipped multi-purpose drill Drill Ø 5 mm	787000 5
Carbide-tipped multi-purpose drill Drill Ø 6 mm	787000 6
Carbide-tipped multi-purpose drill Drill Ø 8 mm	787000 8
"CYL-9" carbide-tipped multi-purpose drill Drill Ø 10 mm	787005 10
"CYL-9" carbide-tipped multi-purpose drill Drill Ø 12 mm	787005 12
"CYL-9" carbide-tipped multi-purpose drill Drill Ø 3 mm	787005 3
"CYL-9" carbide-tipped multi-purpose drill Drill Ø 4 mm	787005 4
"CYL-9" carbide-tipped multi-purpose drill Drill Ø 5 mm	787005 5

"CYL-9" carbide-tipped multi-purpose drill Drill Ø 6 mm	787005 6
"CYL-9" carbide-tipped multi-purpose drill Drill Ø 8 mm	787005 8
Carbide-tipped multi-purpose drill set Number of drills 7	787010 7
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 10 mm	787060 10
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 12 mm	787060 12
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 6 mm	787060 6
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 8 mm	787060 8
"CYL-9" carbide-tipped multi-purpose drill long Drill Ø 10 mm	787065 10
"CYL-9" carbide-tipped multi-purpose drill long Drill Ø 12 mm	787065 12
"CYL-9" carbide-tipped multi-purpose drill long Drill Ø 6 mm	787065 6
"CYL-9" carbide-tipped multi-purpose drill long Drill Ø 8 mm	787065 8
Carbide-tipped multi-purpose drill Drill Ø 10 mm	787040 10
Carbide-tipped multi-purpose drill Drill Ø 12 mm	787040 12
Carbide-tipped multi-purpose drill Drill Ø 4 mm	787040 4
Carbide-tipped multi-purpose drill Drill Ø 5 mm	787040 5
Carbide-tipped multi-purpose drill Drill Ø 6 mm	787040 6
Carbide-tipped multi-purpose drill Drill Ø 8 mm	787040 8
Carbide-tipped multi-purpose drill long Drill Ø 10 mm	787045 10
Carbide-tipped multi-purpose drill long Drill Ø 12 mm	787045 12
Carbide-tipped multi-purpose drill long Drill Ø 6 mm	787045 6
Carbide-tipped multi-purpose drill long Drill Ø 8 mm	787045 8
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 10 mm	787047 10
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 4 mm	787047 4

Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 5 mm	787047 5
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 6 mm	787047 6
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 8 mm	787047 8
Carbide-tipped multi-purpose drill set Drill Ø 4-10 mm	787050 4-10
Carbide-tipped multi-purpose drill set long Drill Ø 6-12 mm	787055 6-12
Carbide-tipped multi-purpose drill bit set, 1/4 inch (E 6.3) Drill Ø 4-10 mm	787057 4-10