



Hammer drill, Type: GBH540DCE



Order data

Order number	075510 GBH540DCE
GTIN	3165140461214
Item class	03B

Description

Version:

Large all-purpose hammer drill with powerful impact mechanism (8.8 J impact energy) and **SDS-max tool holder**.

- **Vibration control vibration damping ensures pleasant working, even on time-consuming tasks.**
- **Automatic switch lock for maximum operator convenience during continuous chiselling work.**
- **Constant electronics, service display and standby display for maximum working convenience.**
- **Adjustment wheel for setting the rotation speed and impact rate, for optimum performance.**

Advantage:

Vibration control.

Supplied with:

With additional handle, machine cloth. Including tube of grease, additional handle, machine cloth and case.

Note:

Suitable carbide hammer drills can be found from No. 787000. Suitable spare batteries and chargers can be found under No. 073851 – 073866.

Technical description

Power consumption	1150 W
-------------------	--------

Manufacturer's designation	GBH 5-40 DCE
Impact energy	8.8 J
Tool arbor shape	SDS Max
maximum hammer rate	3050 min ⁻¹
maximum twist drill size Ø in concrete	40 mm
maximum vibration to EN	10.5 m/s ²
Weight	6.8 kg
Shank	SDS Max
Packaging	Carrying case
Power supply	Mains operated
Suitable for material	Stone
Suitable for material	Steel
Suitable for material	Concrete
Suitable for material	Masonry
Type of product	Hammer drill

Accessories

Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 4 mm	787047 4
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 12 mm	787060 12
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 10 mm	787047 10
Carbide-tipped multi-purpose drill long Drill Ø 12 mm	787045 12
Carbide-tipped multi-purpose drill Drill Ø 4 mm	787040 4
Carbide-tipped multi-purpose drill set Drill Ø 4-10 mm	787050 4-10
Carbide-tipped multi-purpose drill Drill Ø 10 mm	787040 10
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 10 mm	787060 10

Carbide-tipped multi-purpose drill long Drill Ø 6 mm	787045 6
Carbide-tipped multi-purpose drill Drill Ø 8 mm	787040 8
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 5 mm	787047 5
Carbide-tipped multi-purpose drill set long Drill Ø 6-12 mm	787055 6-12
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 6 mm	787047 6
Carbide-tipped multi-purpose drill Drill Ø 6 mm	787040 6
Carbide-tipped multi-purpose drill Drill Ø 12 mm	787040 12
Carbide-tipped multi-purpose drill bit, 1/4 inch (E 6.3) Drill Ø 8 mm	787047 8
Carbide-tipped multi-purpose drill long Drill Ø 10 mm	787045 10
Carbide-tipped multi-purpose drill Drill Ø 5 mm	787040 5
Carbide-tipped multi-purpose drill long Drill Ø 8 mm	787045 8
Carbide-tipped multi-purpose drill bit set, 1/4 inch (E 6.3) Drill Ø 4-10 mm	787057 4-10
Carbide-tipped multi-purpose drill long with SDS-plus shank socket Drill Ø 8 mm	787060 8