

**TMSERROR, Type: GBH18VEC****Order data**

Order number	075515 GBH18VEC
GTIN	3165140862417
Item class	03B

Description**Version:**

18-V cordless hammer drill with **SDS-plus tool mounting** and Bosch **Electronic Cell Protection (ECP)**: Protects the battery against overloading, overheating and deep discharge. Innovative CoolPack batteries ensure optimum heat dissipation (increases the service life).

- **Efficient maintenance-free EC motor (brushless).**
- **The highest chiselling rate (12kg/hour) in its class.**
- **Overload clutch to protect both user and machine.**
- **Reversible.**
- **Extremely sturdy: Electronic Motor Protection switches off the motor if it is overloaded. Fully operational even after a drop test from 2 m on to concrete.**

Advantage:

Optimised ratio between power and weight.

Supplied with:

Including 2 × 18V / 5.0 Ah Li-ion battery, charger, depth stop, 1/1 L-BOXX inlay for device and charger and L-Boxx.

Note:

Suitable carbide hammer drills can be found from No. 787000. Suitable spare batteries and chargers can be found under No. 073851 – 073866.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 18 V

Shank: SDS Plus

Manufacturer's designation: GBH 18 V-EC

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 5 A·h

Battery voltage: 18 V

maximum twist drill size Ø in steel: 13 mm

Technical description

Impact energy	1.7 J
Battery voltage	18 V
maximum twist drill size Ø in concrete	18 mm
maximum vibration to EN	16 m/s ²
maximum hammer rate	4550 min ⁻¹
Battery capacity	5 A·h
Tool arbor shape	SDS-Plus
maximum twist drill size Ø in wood	20 mm
Manufacturer's designation	GBH 18 V-EC
suitable battery - supplier / battery type / voltage	Bosch 18 V
Weight	2.6 kg
maximum twist drill size Ø in steel	13 mm
Packaging	Modular case (L-Boxx)
Shank	SDS Plus
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Power supply	Rechargeable battery-powered
Suitable for material	Stone
Suitable for material	Concrete
Suitable for material	Masonry
Type of product	Hammer drill

Accessories

Li-ion battery Battery type, battery voltage B18 V	073854 B18
Battery charger Type AL1860CV	073866 AL1860CV
Carbide-tipped multi-purpose drill Drill Ø 5 mm	787000 5
Carbide-tipped multi-purpose drill Drill Ø 4 mm	787000 4
Carbide-tipped multi-purpose drill Drill Ø 8 mm	787000 8
Carbide-tipped multi-purpose drill Drill Ø 3 mm	787000 3
Carbide-tipped multi-purpose drill Drill Ø 12 mm	787000 12
Carbide-tipped multi-purpose drill Drill Ø 6 mm	787000 6
Carbide-tipped multi-purpose drill Drill Ø 10 mm	787000 10
Battery charger Type 1880CV	073866 1880CV