



Snipe-nose combination pliers chrome-plated, with grips, overall length: 145mm



Order data

Order number	701650 145
GTIN	4003773078975
Item class	73F

Description

Version:

Gripping faces with special three-point contour for secure gripping of flat parts. Fast cutting thanks to high ratio compound action. Milled slot in the gripping area enables small workpieces such as nails, pins and bolts to be held and pulled. Handy for working in inaccessible locations. Slim head profile with tapered jaws.

Standard:

DIN ISO 5746.

Material:

Special tool steel.

Technical description

Cutting capacity hard wire up to \emptyset	2 mm
Cutting capability medium hard wire up to \emptyset	3 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5746
Handle	Multi-component covering
Material	Special tool steel
Surface	chrome-plated
non-sparking	no

Type of product

Multi-function pliers