

Mitutoyo

Absolute dial indicator Reading 0.01 mm set, 3 pieces, Measuring range: 12,5mm



Order data

Order number	434063 12,5
GTIN	4067263133001
Item class	44A

Description

Version:

Zero point display in any position, e.g. for tolerance measurements. Selectable direction of measurement. 20,000 h continuous operation with one battery.

Function:

IP42: Protected against water falling obliquely (dripping water) up to 15° relative to normal operating position and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Supplied with:

3 x dial indicators No. 434062 size 12,5.

1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497080, spare and special contact points No. 434900; 434910; 434915.

Technical description

Thickness of housing	27.5 mm
Error limit	0.02 mm

Data sheet

IP Index of Protection	IP 42
Measuring range	12.5 mm
#Number of batteries contained	1
Clamping shank Ø h6	8 mm
Body Ø	59 mm
Calibration	C1
#Article no of the battery / rechargeable battery fitted	081560 357
Gauging force	≤ 1.5 N
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Interface	USB interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Type of product	dial gauge

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/434063-12,5>