



LED machine lamp flat, Type: 303mm



Order data

Order number	081438 303
GTIN	4260131238673
Item class	08C

Description

Version:

Sturdy LED machine lamps in an **aluminium casing**, with a satinised acrylic lens for **homogeneous 160-degree illumination**.

- **Low-reflection, non-dazzle and non-flicker.**
- **For connection to a 24 V mains adapter or 24 V machine control system.**

Flat lighting strip, can pivot through 45°.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

With rubber-clad magnets, mains adapter.

Technical description

Illumination	1200 lm
Light output	12 W
Bulb	LED module

Overall height	39 mm
Power supply	Mains operated
Overall length	303 mm
ATEX zone	no
Overall width	40 mm
IP Index of Protection	IP 67
Type of product	Machine lamp