

Garant GRIDLINE

Workbench, left side open, right side 3 drawers, Beech marine ply worktop, 20x20G, Worktop length: 1500mm**Order data**

Order number	920804 1500
GTIN	4062406207069
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Feet with plastic pads, do not damage the floor.

Recessed open housing for ergonomic posture.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

Fitted with:

Drawer front height (right) mm: 125, 150, 250

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite grey, **powder-coated**. **Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Support cabinet width	1300 mm
Height	850 mm
Worktop length	1500 mm
Drawer usable width in G	20
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Series	Ready-to-go
Worktop thickness	50 mm
Number of drawers	3
Drawer usable depth in G	20
Drawer usable width	500 mm
Drawer body usable height	525 mm
Worktop depth	750 mm
Drawer usable area in G	20×20
Drawer usable depth	500 mm
Support cabinet depth	700 mm
Weight	126 kg
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Disassembly tool Type 1	950070 1
Mat for drawers Dimension in G 20X20	951830 20X20
Lock plate for GridLine Type KO21	914227 KO21
Slotted dividers / plain dividers set Drawer front height / type 150/4	950320 150/4
Drawer Drawer front height 150 mm	927800 150
Slotted dividers / plain dividers set Drawer front height / type 125/6	950320 125/6
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Drawer Drawer front height 250 mm	927800 250
Drawer Drawer front height 125 mm	927800 125
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Non-slip mats set for drawers,5 pieces Dimension in G 20X20	951885 20X20
Slotted dividers / plain dividers set Drawer front height / type 125/4	950320 125/4
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Slotted dividers / plain dividers set Drawer front height / type 125/1	950320 125/1
Slotted dividers / plain dividers set Drawer front height / type 150/5	950320 150/5
Pliers set Number of tools 5	954305 5
Slotted dividers / plain dividers set Drawer front height / type 125/3	950320 125/3
Pliers set Number of tools 5	954306 5