

Storage shelf rack 1 basic rack, 2 extension racks, Depth 500 mm, Height / storage shelf width: 2000/1000mm



Order data

Order number	990532 2000/1000
GTIN	
Item class	96P

Description

Version:

T-profile frames and storage shelves galvanised. Available with a maximum **shelf load capacity** of 150 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

Bay load: 1300 kg at height of 2000 mm.

Application:

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

Note:

- **Clamping feet are supplied.**
- **Floor and wall fastenings not supplied.**
- **Access from one side only, due to use of diagonal braces.**
- **The free unsupported length (K) must not be more than 600 mm.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Number of shelves	15
Assembled size	3072x536 mm

Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanized
Product name attribute	Depth 500 mm
Type of product	Storage shelf