

**Reversible precision ratchet, 1/4 inch, Type: 1/4****Order data**

Order number	632389 1/4
GTIN	4000896226917
Item class	630

Description**Version:**

With reversing lever for right-hand and left-hand threads, working arc 4°.

Material selection and special forging method guarantee optimal functioning and long life.

Standard:

Außenvierkante nach **DIN 3120-A 6,3** mit federnder Kugel, Innenvierkante nach **DIN 3120**.

Material:

Chrome vanadium steel, chrome-plated.

Suitable for:

Manual use.

Technical description

Square drive	1/4 in
Standard	DIN 3120
overall length	116 mm
No. of teeth	90
Working angle	4 degrees
Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Ratchet