

Garant
Workshop set, Number of tools: 22

Order data

Order number	955071 22
GTIN	4062406207168
Item class	91A

Description
Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer is anthracite, the underlying contrast colour is grey, thus indicates any missing tools.

Rigid foam inlay basic set for one complete drawer – usable area 20×20G.

Suitable for:

GridLine Ready-to-go workbenches, GridLine Vario workbenches with 24G casing, GridLine 24G casing, GridLine 24×24G tool cabinets, GridLine 20×20G drawers, GridLine XL ToolCar No. 914590.

Supplied with:

Rigid foam inlay, empty No. 952001 size 955071: 1 pc.

GARANT caliper No. 410100 size 150: 1 pc.

GARANT external micrometer No. 420402 size 0 – 25: 1 pc.

GARANT tape measure No. 462201 size 2.5: 1 pc.

GARANT spirit level No. 467010 size 250: 1 pc.

GARANT double open ended spanner No. 610600 size 8×9; 10×11; 12×13; 14×15; 17×19: 1 pc. each

GARANT hexagon key L-wrench with retention ball No. 627132 size 9: 1 pc.

GARANT slot-head screwdriver No. 660030 size 2.5; 4; 5.5: 1 pc. each

GARANT screwdriver for Phillips No. 667690 size 1; 2: 1 pc. each
 GARANT screwdriver holder with 1/4-inch bits with magnet No. 676663 size 10: 1 pc.
 GARANT combination pliers No. 700940 size 160: 1 pc.
 GARANT side cutter No. 724840 size 160: 1 pc.
 GARANT engineer's hammer No. 750110 size 200: 1 pc.
 GARANT heavy duty scissors No. 769240 size 175: 1 pc.
 GARANT pliers wrench No. 813501 size 180: 1 pc.
 GARANT universal knife No. 845020: 1 pc.
 Smallest suitable drawer front height: 100 mm
 Drawer usable area in G: 20x20
 Width: 500 mm
 Depth: 500 mm
 Width in G: 20
 Depth in G: 20

Technical description

Depth in G	20
Drawer usable area in G	20x20
Depth	500 mm
Width	500 mm
Width in G	20
Number of tools	22
Version	for roller cabinet drawer
suitable for drawer front height	100 mm
suitable for drawer front height	125 mm
suitable for drawer front height	150 mm
suitable for drawer front height	200 mm
suitable for drawer front height	250 mm
suitable for drawer front height	300 mm
Rigid foam quality LD45, thickness	30 mm
Square drive	1/4 in
Smallest suitable drawer front height	100 mm
Type of product	Rigid foam inlay

Accessories

General-purpose knife with 2-component handle with 3 blades, 18 mm	845020
Double open ended spanner Jaw widths 17X19 mm	610600 17X19
Rigid foam inlay for tool sets suitable for rigid foam set 955071	952001 955071
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 1	667690 1
Double open ended spanner Jaw widths 8X9 mm	610600 8X9
Pliers wrench overall length 180 mm	813501 180
Tape measure with viewing window Band length 2,5 m	462201 2,5
External micrometer Measuring range 0-25 mm	420402 0-25
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 2	667690 2
Double open ended spanner Jaw widths 10X11 mm	610600 10X11
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 4 mm	660030 4
Bit-holding driver with magazine with 1/4 inch bits with magnet Blade length 10 mm	676663 10
Double open ended spanner Jaw widths 12X13 mm	610600 12X13
Engineer's hammer with handle protection collar Weight without handle 200 g	750110 200
Diagonal side cutter chrome-plated, with grips overall length 160 mm	724840 160
Spirit level with selectable magnet Length 250 mm	467010 250
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 2,5 mm	660030 2,5
Hexagon key L-wrench set, with retainer ball chrome-plated Number of screwdrivers 9	627132 9
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 5,5 mm	660030 5,5

Heavy-duty scissors with titanium coating overall length 175 mm	769240 175
Vernier caliper Measuring range 150 mm	410100 150
Double open ended spanner Jaw widths 14X15 mm	610600 14X15
Combination pliers, chrome-plated, with 2-component grips overall length 160 mm	700940 160