



## Workshop set, Number of tools: 26



### Order data

Order number	955081 26
GTIN	4062406207182
Item class	91A

### Description

#### Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer is anthracite, the underlying contrast colour is grey, thus indicates any missing tools.

Rigid foam inlay basic set for one complete drawer – usable area 20×20G.

#### Suitable for:

GridLine Ready-to-go workbenches, GridLine Vario workbenches with 24G casing, GridLine 24G casing, GridLine 24×24G tool cabinets, GridLine 20×20G drawers, GridLine XL ToolCar No. 914590.

#### Supplied with:

Rigid foam inlay, empty No. 952001 size 955081: 1 pc.

HOLEX LED torch No. 081437 size BLACK: 1 pc.

HOLEX digital caliper ABS No. 412821 size 150: 1 pc.

HOLEX external micrometer No. 420200 size 0–25: 1 pc.

HOLEX locking tape measure No. 462010 size 3: 1 pc.

HOLEX spirit level No. 467435 size 300: 1 pc.

HOLEX double open-ended spanner No. 610950 size 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×21; 19×22: 1 pc. each

HOLEX hexagon key L-wrench set, No. 627225 size 9: 1 pc.

HOLEX screwdriver for slot-head with power grip No. 660701 size 3.5; 5.5; 8: 1 pc. each

HOLEX short screwdriver for slot-head No. 664201 size 5.5: 1 pc.  
 HOLEX screwdriver for Phillips with power grip No. 668401 size 1; 2; 3: 1 pc. each  
 HOLEX stub screwdriver for Phillips No. 668471 size 2: 1 pc.  
 HOLEX combination pliers, vanadium No. 702995 size 160: 1 pc.  
 HOLEX water pump pliers No. 706145 size 250: 1 pc.  
 HOLEX snipe-nose pliers No. 713195 size 160: 1 pc.  
 HOLEX engineer's hammer No. 750125 size 300: 1 pc.

## Technical description

Number of tools	26
Drawer usable area in G	20×20
Width in G	20
Depth	500 mm
Depth in G	20
Width	500 mm
Power supply	Battery-powered
Version	for roller cabinet drawer
suitable for drawer front height	100 mm
suitable for drawer front height	125 mm
suitable for drawer front height	150 mm
suitable for drawer front height	200 mm
suitable for drawer front height	250 mm
suitable for drawer front height	300 mm
Rigid foam quality LD45, thickness	30 mm
Smallest suitable drawer front height	100 mm
Type of product	Rigid foam inlay

## Accessories

Screwdriver for Phillips, short Cross-head size 2	668471 2
Engineer's hammer Weight without handle 300 g	750125 300

LED torchwith batteries Colour BLACK	081437 BLACK
Double open ended spanner Jaw widths 18X21 mm	610950 18X21
Tape measure Band length 3 m	462010 3
Screwdriver for slot-head, with power grip Blade width b 8 mm	660701 8
Snipe-nose pliers, straight, bright finished, with grips Overall length 160 mm	713195 160
Hexagon key L-wrench setnickel-plated Number of screwdrivers 9	627225 9
External micrometer Measuring range 0-25 mm	420200 0-25
Screwdriver for Phillips, with power grip Cross-head size 1	668401 1
Double open ended spanner Jaw widths 19X22 mm	610950 19X22
Screwdriver for Phillips, with power grip Cross-head size 3	668401 3
Double open ended spanner Jaw widths 14X15 mm	610950 14X15
Double open ended spanner Jaw widths 6X7 mm	610950 6X7
Vanadium combination pliers, bright finished, with two-part grips Overall length 160 mm	702995 160
Rigid foam inlay for tool sets suitable for rigid foam set 955081	952001 955081
Screwdriver for slot-head, short Blade width b 5,5 mm	664201 5,5
Double open ended spanner Jaw widths 8X9 mm	610950 8X9
Water pump pliers chemically blacked, with coated grips Overall length 250 mm	706145 250
Double open ended spanner Jaw widths 10X11 mm	610950 10X11
Aluminium spirit level Length 300 mm	467435 300
Screwdriver for slot-head, with power grip Blade width b 5,5 mm	660701 5,5
Digital caliperABS Measuring range 150 mm	412821 150
Screwdriver for Phillips, with power grip Cross-head size 2	668401 2
Double open ended spanner Jaw widths 12X13 mm	610950 12X13
Screwdriver for slot-head, with power grip Blade width b 3,5 mm	660701 3,5

Double open ended spanner Jaw widths 16X17 mm

610950 16X17