



## Tap wrench, adjustable, Type: 3



### Order data

Order number	148410 3
GTIN	4062406208202
Item class	12L

### Description

#### Version:

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **standard** use: Zinc die-cast body.

### Technical description

for hand reamer Ø DIN 206	6.5 - 15 mm
Overall length	370 mm
for hand taps DIN 352	M5 – M20
Capacity □	4.9 - 12 mm
Standard	DIN 1814
Type of product	Tap wrench