



Tap wrench, adjustable, Type: 1.1/2



Order data

Order number	148410 1.1/2
GTIN	4062406208189
Item class	12L

Description

Version:

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **standard** use: Zinc die-cast body.

Technical description

for hand reamer Ø DIN 206	2.5 - 9.5 mm
Capacity □	2 - 8 mm
Overall length	175 mm
for hand taps DIN 352	M1 – M12
Standard	DIN 1814
Type of product	Tap wrench